

Locking Devices, Twist-Lock®, Watertight Safety Shroud, Flanged Inlet, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30P, Screw Terminal

By Hubbell Wiring Device-Kellems
Catalog # [HBL2745SW](#)

Watertight Safety-Shroud®, Locking Devices, Twist-Lock®,
Flanged Inlet, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire
Grounding, NEMA L17-30P, Screw Terminal , Gray



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17
- Environmental - Moisture Resistance - Type 4, 4X, 12, IP66 suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2745SW
Color	Gray, White
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	30A Watertight Safety-Shroud® Flanged Inlet
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless Steel• Blades - Brass• Housing / Flange - Gray PBT• Mounting Screw - Stainless Steel• Terminal Retainer - Clear polycarbonate• Terminal Screws - #10-32 Brass (Phillips / Slotted /

Type	Robertson)
UPC	Flanged Inlet 783585232041

Dimensions

Dimensions	3.75 in x 3.75 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.75 in
Weight	0.65 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L17-30P

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand