



Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Wye120/208V AC, 4-Pole 4-Wire Non- Grounding, L18-20R, Screw Terminal, Black.

By Hubbell Wiring Device-Kellems
Catalog # [HBL2750](#)



Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Wye120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-20R, Screw Terminal, Black.

Features

- High-impact, abuse-resistant nylon face
- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Application

Heavy Duty Industrial

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Non-Grounding Single Flush Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)

Dimensions

Dimensions	3.28 in x 1.7 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	3.28 in
Weight	0.3 lb
Width	1.7 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	L18-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Single Flush Receptacle
- Single Flush Receptacle

UPC

783585236193



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL2750-SPEC-EN | REV 1/2024