

# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 125V, 5- 15R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # BR15I



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5-15R, Ivory, Single Pack.

## Application

- Commercial Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

|                              |  |
|------------------------------|--|
| Catalog Number               | BR15I  |
| Color                        | Ivory  |
| EU RoHS Indicator            | Yes  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means  |
| Horsepower - Maximum         | 0.5  |
| Item Type                    | Traditional Duplex   |
| Material                     | Nylon  |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 2-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact   |
| Series                       | Commercial Specification Grade   |
| Specifications               | <ul style="list-style-type: none"> <li>• Automatic Self-grounding Staple - Stainless steel</li> <li>• Base - Nylon</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> </ul> |

- Mounting Screws - Galvanized Steel
- Mounting Strap - .040 in. (1) Galvanized steel
- Power Contacts - .030 in. (.8) Brass
- Terminal Screws - Plated steel
- Wire Clamp - .062 in. (1.6) Nickel plated steel

Style  
Type  
UPC

Smooth Face  
Standard Duplex  
783585834849

## Dimensions

|              |                           |
|--------------|---------------------------|
| Dimensions   | 3.3 in x 1.34 in x 1.1 in |
| Display Size | Standard Sized Product    |
| Height       | 1.1 in                    |
| Length       | 3.3 in                    |
| Weight       | 0.25 lb                   |
| Width        | 1.34 in                   |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 15 A                      |
| Connectivity               | Back and Side Wired       |
| Current / Amperage Rating  | 15 A                      |
| Current Rating             | 15 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 125 V                     |
| Voltage Rating Description | 125 V                     |
| Wattage                    | 1875 W                    |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |

## Certifications And Compliance

Industry Standard(s)

- Certified to CSA 22.2, No. 42
- Fed. Spec. W-C-596
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating

5-15R

Standards - RoHS Compliance

CM

Status

## Logistics

Carton Quantity

10

Pallet Quantity

9000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - BR15I](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-BR15I-SPEC-EN | REV 10/2024