

## Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 3-Phase Wye 347/600V AC, 4-Pole 4-Wire Non-Grounding, L20-30P, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2775](#)

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 3-Phase Wye 347/600V AC, 4-Pole 4-Wire Non-Grounding, L20-30P, Screw Terminal, White



### Application

Extra Heavy Duty Industrial

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C. Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL2775
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Non-Grounding Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Steel - nickel plated</li> <li>• Blades - Brass</li> <li>• Housing / Flange - Nylon</li> <li>• Mounting Screw - Nickel plated brass</li> </ul>

Type  
UPC

- Terminal Clamp - Cold rolled steel - nickel plated
  - Terminal Retainer - Clear polycarbonate
  - Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Flanged Inlet  
783585039534

### Dimensions

Dimensions	3.06 in x 3.06 in x 2.27 in
Display Size	Standard Sized Product
Height	2.27 in
Length	3.06 in
Weight	0.3 lb
Width	3.06 in

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	3 Phase WYE 347/600 VAC
Voltage Rating Description	3 Phase WYE 347/600 VAC

### Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating L20-30P  
Standards - RoHS Compliance CM  
Status

**Logistics**

Carton Quantity 10

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL2775](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2775-SPEC-EN | REV 1/2025