

Straight Blade Devices, Receptacles, Weather-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown

By Hubbell Wiring Device-Kellems
Catalog # [BR15WR](#)



Straight Blade Devices, Receptacles, Weather-Resistant Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15R, Brown, Single Pack.

Application

- Commercial Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	BR15WR
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Weather Resistant
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Stainless steel

- Mounting Screws - Stainless steel
 - Power Contacts - .030 in. (.8) Brass
 - Terminal Screws - Stainless steel
 - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Smooth Face
Weather Resistant
783585144467

Style
Type
UPC

Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.15 lb
Width	0.83 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA C22.2, No. 42
- Fed. Spec. W-C-596
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating

5-15R

Logistics

Carton Quantity

10

Pallet Quantity

9000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - EdgeConnect™ Technology FAQ](#)

[Specifications - BR15WR](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-BR15WR-SPEC-EN | REV 10/2024