

Locking Devices, Twist-Lock®,  
Watertight Safety Shroud,  
Receptacle, 30A 3-Phase Wye  
120/208V AC, 4-Pole 5-Wire  
Grounding, L21-30R, Screw  
Terminal

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2810SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®,  
Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire  
Grounding, NEMA L21-30R, Screw Terminal, PBT housing and  
flange, Gray.

Application

Heavy Duty Industrial Shrouded Watertight

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2810SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	3
Item Type	30A Watertight Safety-Shroud® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Body Contact Carrier - Natural (white) nylon</li><li>• Contacts - Brass</li><li>• Drive Screws - Steel, zinc plated</li><li>• Housing / Cover - Gray RPT</li></ul>



Type	Receptacle
UPC	783585232065
• Lift-Cover Spring & Pin -	Stainless Steel
• Terminal Retainer - Clear	polycarbonate

Dimensions

Dimensions	3.75 in x 3.75 in x 2.91 in
Display Size	Standard Sized Product
Height	2.91 in
Length	3.75 in
Weight	0.65 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3-Phase Y 120/208 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L21-30R

Logistics

Product Assets

Catalogs - WDK Catalog Full 2024  
Specifications - HBL2810SW  
Warranty - Industrial & Commercial Products

