



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 16A 100-130V, 2-Pole 3-Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems
 Catalog # [HBL316C4W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 16A 100-130V, 2-Pole 3-Wire Grounding, Terminal Screws, Yellow, Watertight

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Connections

General

Color	Yellow
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - 3000V AC • Electrical - Max. Working Voltage - 600V RMS • Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Watertight per IEC 60309-1 • Environmental - Operating Temperatures - Maximum Continuous 75°C • Minimum - 40°C w/o impact • Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682 • Mechanical - Product

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Voltage Rating	100-130 VAC
Voltage Rating Description	100-130 VAC

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146033
----------------------	--

Nema Rating Non-NEMA

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identification -
Identification and ratings
are a permanent part of
the device housing

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with North American and
IEC conventions

Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585403205



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL316C4W-SPEC-EN | REV 1/2024