

# Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # CR20I



Straight Blade Devices, Receptacles, Duplex, Commercial Grade,  
2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.

## Application

- Commercial Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	CR20I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"> <li>Automatic Self-grounding Staple - Stainless steel</li> <li>Base - Nylon</li> <li>Face - Nylon</li> <li>Mounting Screws - Galvanized steel</li> <li>Mounting Strap - .040 in. (1) Galvanized steel</li> </ul>

- Power Contacts - .030 in. (.8) Brass
- Terminal Screws - Plated steel

Style	Smooth Face
Type	Standard Duplex
UPC	783585900155

## Dimensions

Dimensions	1.32 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.2 lb
Width	0.83 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>Certified to CSA, C22.2, No. 42</li> <li>Fed. Spec. W-C-596</li> <li>NEMA® WD-6 Compliant</li> <li>UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-20R

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - CR20I](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-CR20I-SPEC-EN | REV 10/2024