

HUBBELL
Wiring Device-Kellems

**Switches and Lighting Controls,
Industrial Grade, Fused
Disconnects, Heavy Duty, Three
Pole, 60 600V AC, Terminal Screws,
Gray**

By Hubbell Wiring Device-Kellems
Catalog # [FDS60](#)

Industrial Grade, Fused Disconnects, Heavy Duty, 3-Pole, 60
600V AC, Terminal Screws



General

Catalog Number	FDS60
Color	
EU RoHS Indicator	No
Horsepower - Maximum	40
Ingress Protection	IP66
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Dielectric Voltage - Withstands 3000V AC minimum Electrical - Max. Working Voltage - 600V AC RMS Environmental - Flammability - UL94-5VA and VO Classification Environmental - Moisture Resistance - Indoor and Outdoor - Type 4X, Indoor - Type 12 Environmental - Operating Temperature - Max. continuous 75°C, Min. Continuous -40°C w/o impact Environmental - UV Resistance - All materials are UV stabilized Mechanical - Impact Resistance - In accordance with UL 746C Mechanical - Mounting - External fully adjustable feet Mechanical - Product Identification - Identification and ratings are part of external label Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions
Series	Fused
Style	Heavy Duty
Type	Disconnect Switches
UPC	783585519609

Dimensions

Dimensions	15.36 in x 11.46 in x 8.43 in
Height	8.43 in
Length	15.36 in
Weight	16.85 lb
Width	11.46 in

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	1
Pallet Quantity	35

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-FDS60-SPEC-EN | REV 6/2024