

# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 20A 125V AC, 2-Pole 3- Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL320R4W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 20A 125V AC, 2-Pole 3- Wire Grounding, Terminal Screws, Yellow, Watertight



## Application

High Ampacity Watertight Connections

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Electrical - Temperature Rise - Max. 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

## General

Catalog Number	HBL320R4W
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Cover - Reinforced Thermoplastic Polyester</li> </ul>

Style  
Type  
UPC

- Cover Screw - Nickel-plated brass
  - Gaskets - Solid Neoprene
  - Housing - Zytel® 101 Nylon
  - Mounting Flange - Zytel® 101 Nylon
- Standard Service  
Watertight Receptacle  
783585403427

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Standard C22.2 No. 182.1</li> <li>• UL Classified to IEC 60309-1 IEC 60309-2</li> <li>• UL Listed, File E146032</li> </ul>
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
Pallet Quantity	640



A Hubbell brand