

# Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 250/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3335C](#)

Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 250/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, White.

## Application

Insulgrip

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL3335C
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Non- Grounding Insulgrip® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Contacts - Brass</li><li>• Housing - Nylon</li><li>• Mounting Screw - Nickel plated brass</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li></ul>



Type  
UPC

- Terminal Retainer - Clear polycarbonate
  - Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Flanged Receptacle  
783585039862

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.22 in
Display Size	Standard Sized Product
Height	2.22 in
Length	2.88 in
Weight	0.25 lb
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----



A Hubbell brand