



Wiring Device-Kellems

Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Double Throw 10A 250V/10A 125V, Terminal Screws,

By Hubbell Wiring Device-Kellems
Catalog # [HBL12](#)



Switches and Lighting Controls, Commercial Grade, Panel Mount and Specialty Switches, Bat Handle Switches, Single Pole Double Throw 10A 250V/10A 125V, Terminal Screws,

Features

- Nickel Plated for Corrosion Resistance

General

Action	SPDT
Horsepower - Maximum	0.75
Item Type	Panel Mount and Bat Handle Switch
Mounting Method	Panel Mount
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Environmental - Operating Temperatures - Max Continuous- 75 °C, Minimum -40 °C Without Impact
Series	Single Pole/Double Throw
Style	Screw Terminal
Type	General Purpose
UPC	783585016740

Dimensions

Dimensions	2.09 in x 0.56 in x 1.12 in
Height	1.12 in
Length	2.09 in
Weight	0.05 lb
Width	0.56 in

Electrical Ratings

Amperage Rating	10/20 A
Connectivity	Screw Terminals
Current / Amperage Rating	10/20 A
Voltage Rating	250/125 VAC

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.