

By Hubbell Wiring Device-Kellems
Catalog # [HBL363C6W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female
Connector Body, 63A 220-240V, 2-Pole 3-Wire Grounding,
Terminal Screws, Watertight



Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL363C6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Cord Clamps - Reinforced Thermoplastic Polyester• Covers - Reinforced Thermoplastic Polyester• Gaskets - Solid Neoprene• Glands - Solid Neoprene

Style	Housing - Zytel® ST801 Nylon
Temperature Rating	Standard Service Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585403892

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	63 A
Current Rating	63 A
Voltage Rating	220-240 VAC
Voltage Rating Description	220-240 VAC

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed, File E146033
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL363C6W](#)