

HUBBELL
Wiring Device-Kellems

**Extra Heavy Duty Industrial Grade,
Locking Toggle Switches, General
Purpose AC, Single Pole, 15A
120/277V AC, Back and Side Wired
Key Guide**

By Hubbell Wiring Device-Kellems
Catalog # [HBL1201L](#)

Switches and Lighting Controls, Extra Heavy Duty Industrial
Grade, Locking Toggle Switches, General Purpose AC, Single
Pole, 15A 120/277V AC, Back and Side Wired, Black Key Guide



General

Application	Back and Side Wired
Catalog Number	HBL1201L
Color	Black
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
	Electrical - Max. Continuous Current - 15A
	Electrical - Max. Working Voltage - 277V AC
	Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
	Electrical - Temperature Rise - 30°C maximum at rated current
	Environmental - Flammability - UL 94V-2
	Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
	Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only
Series	Extra Heavy Duty
Style	Single Pole
Type	Locking
	Locking
UPC	783585430089

Dimensions

Dimensions	4.06 in x 1.31 in x 1.13 in
Height	1.13 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1201L-SPEC-EN | REV 6/2024