

Replaced by HBL3PS50ALU, Surge Protective Devices, SPIKESHIELD Surface Mount Block, 50KA, 120/240V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL3W50](#)



Surge Protective Devices, SPIKESHIELD Surface Mount Block, 50KA, 120/240V AC

Application

Surface Mount Brick with Leads

Performance

- Electrical - Diagnostics - Green Status LED per line
- Electrical - Surge Current per Phase - 50kA
- Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
- Mechanical - Terminal Accommodation - #12 AWG Wire Leads

General

| | |
|------------------------------|---|
| Catalog Number | HBL3W50 |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor and Outdoor |
| Indicator(s) Type | Green Status LED per Line |
| Item Type | Wired-In Surge Arrestors |
| Material | Steel |
| Material - Mounting Hardware | Mounting Screws |
| Operating Temperature | -40 Degrees F to 149 Degrees F (-40 C to 65 C) |
| Response Time | 5 |
| Series | Wired-In Surge Devices |
| Specifications | <ul style="list-style-type: none">• Dimensions - 2.7"D x 3.0"W x 3.6"H• Frequency - 50/60 Hz• NEMA - Type 4X• Warranty - 10 year |

| | |
|------|----------------------|
| Type | • Weight - 1.8 lbs |
| UPC | 50kA 783585120850 |

Dimensions

| | |
|--------------|-----------|
| Display Size | 50kA Peak |
|--------------|-----------|

Electrical Ratings

| | |
|----------------------------|---|
| Connectivity | Leads |
| Frequency Rating | 60 Hz |
| Phase | Single Phase |
| Voltage Rating | <ul style="list-style-type: none">• Single Phase 120 VAC• Single Phase 240 VAC |
| Voltage Rating Description | 120/240 VAC Single Phase |

Certifications And Compliance

| | |
|----------------------|--------------------|
| Industry Standard(s) | UL1449-3rd Edition |
|----------------------|--------------------|

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 20 |
| Pallet Quantity | 840 |

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Residential Catalog](#)
[Specifications - HBL3W50](#)
[Warranty - SPD Series: 320kA, 160kA, 100kA, 120kA, 80MkA & 50kA](#)