

**HUBBELL**  
Wiring Device-Kellems

**Switches and Lighting Controls,  
Industrial Grade, PresSwitch,  
General Purpose AC, Three Way,  
20A 120/277V AC, Screw Terminals,  
Brown**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1283](#)

Switches and Lighting Controls, Industrial Grade, PresSwitch,  
General Purpose AC, Three Way, 20A 120/277V AC, Screw  
Terminals, Brown



## General

Action	SPDT
Catalog Number	HBL1283
Color	Brown
EU RoHS Indicator	Yes
Item Type	Three Way Toggle Switch
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute Electrical - Max. Continuous Current - 20A Electrical - Max. Working Voltage - 277V AC Electrical - Overload - Minimum 4.8 times rated current for 100 cycles Electrical - Temperature Rise - 30°C maximum at rated current Environmental - Flammability - UL 94V-2 Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only
Series	General Purpose
Style	Three Way
UPC	783585016870

## Dimensions

Dimensions	3.28 in x 1.5 in x 1.45 in
Height	1.45 in
Length	3.28 in
Weight	0.2 lb
Width	1.5 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL1283-SPEC-EN | REV 6/2024