

Straight Blade Devices, Female Connector Body, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 15A 125V, 5-15R



By Hubbell Wiring Device-Kellems
Catalog # [HBL1547](#)

Straight Blade Devices, Female Connector Body, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.

Application

- Industrial/Commercial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL1547
Color	Yellow
Cord Range	0.230"-0.360" (5.8-18.3)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Elastogrip
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none"> Assembly Screws - Plated steel Contact Holder - Nylon Contacts - .040" (1.0) Brass Housing - Thermoplastic Elastomer Terminal Clamp - Nickel plated steel

Style

Temperature Rating

Type

UPC

Dimensions

Dimensions	3.00 in x 1.61 in x 3.00 in
Display Size	Standard
Height	3 in
Length	3 in
Weight	0.2 lb
Width	1.61 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> CSA Certified to C22.2 No. 42 File 280C NEMA® WD-6 Compliant UL Listed to UL498 File E1706
----------------------	--

- Terminal Retainer - Clear Polycarbonate
- Terminal Screws - #8-32 Brass , multiple drive

Standard

Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

Connector Body

783585013039

Nema Rating 5-15R
Standards - RoHS Compliance CM
Status

Pallet Quantity 4050

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1547](#)
[Warranty - Industrial & Commercial Products](#)

Logistics

Carton Quantity 10



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1547-SPEC-EN | REV 10/2024