

# Single Pole Products, Male Inlet, Threaded Stud Termination, 150 Amp Series, Green

By Hubbell Wiring Device-Kellems  
Catalog # [HBL15MRSGN](#)



Single Pole Products, Male Inlet, Threaded Stud Termination, 150 Amp Series, Green

## Features

- Threaded Stud Termination
- 150 Amp Series
- Green

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

## General

Catalog Number	HBL15MRSGN
Color	Green
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none"><li>• Base Compound - Thermoplastic Elastomer (TPE)</li><li>• Contact Material - Brass</li><li>• Mounting Hole - 3x Ø .20"</li><li>• Retaining Screw Material - Nylon</li><li>• Termination - 5/16-18 Threaded Stud</li></ul>
Style	Male

Type  
UPC

Receptacle, Stud Type  
783585458267

## Dimensions

Display Size  
Standard Sized Product

## Electrical Ratings

Amperage Rating  
Connectivity  
Current / Amperage Rating  
Current Rating  
Phase  
Voltage Rating Description  
Wattage

150 A  
Threaded Stud  
150 A  
150 A  
Single Phase  
600V AC/DC  
90000

## Conductor Related

Number Of Wires  
Wire Size

None  
#4 AWG Type SC/PPC Wire

## Certifications And Compliance

Industry Standard(s)

- National Electric Code (NEC), ANSI/NFPA 70
- UL and cUL Listed
- UL Enclosure Types 3R, 4X, 12

Nema Rating  
Non-NEMA

## Logistics

Carton Quantity  
Pallet Quantity

25  
4500

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Single Pole Devices](#)  
[Specifications - HBL15MRSGN](#)  
[Warranty - Industrial & Commercial Products](#)