

Single Pole Products, Male Inlet, Threaded Stud Termination, 150 Amp Series, Red

By Hubbell Wiring Device-Kellems
Catalog # [HBL15MRSR](#)



Single Pole Products, Male Inlet, Threaded Stud Termination, 150 Amp Series, Red

Features

- Threaded Stud Termination
- 150 Amp Series
- Red

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15MRSR
Color	Red
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer (TPE)• Contact Material - Brass• Mounting Hole - 3x Ø .20"• Retaining Screw Material - Nylon• Termination - 5/16-18 Threaded Stud

Style	Male
Type	Receptacle, Stud Type
UPC	783585458243

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Threaded Stud
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL15MRSR](#)
[Warranty - Industrial & Commercial Products](#)