



Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 200A 600V AC, 3- Pole 4-Wire Grounding Style 2 and Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL4200RS2W](#)



Heavy Duty Insulgrip Pin and Sleeve Devices, Industrial Grade Female Receptacle, 200A 600V AC, 3-Pole 4-Wire Grounding Style 2, Terminal Screws

Features

- Watertight neoprene sealing glands for reliable seal
- Spring-Loaded, gasketed cover for dust-tight seal
- Pin chamber confines arcing within the interior chamber

Application

Metallic with Nylon Shroud

General

| | |
|------------------------------|---|
| Environmental Conditions | Watertight |
| Item Type | Single Flanged-Reversed |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3-Pole |
| Performance | <ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 3,000V AC • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability (Enclosure) - UL 94V-0 and CSA C22.2 No. 0.17 • Environmental - Moisture Resistance - Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94 • Environmental - Operating Temperatures - Max. Continuous 75°C • Min. -40°C w/o impact -25° with impact • Mechanical - Impact Resistance - Per CSA C22.2, No. 182.1, UL 1682 • Mechanical - Product Identification - Identification and ratings |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 200 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 200 A |
| Current Rating | 200 A |
| Phase | Single/Three |
| Voltage Rating | 600 VAC/250 VDC |
| Voltage Rating Description | 600V AC/250V DC |
| Wattage | 120000 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #2 AWG to #4/0 AWG |

Certifications and Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified to CSA Spec. C22.2 No. 182.1 • UL Listed and CSA Certified Type 4X • UL Standard 1682 |
|----------------------|---|

| | |
|------------------------------------|----------|
| Nema Rating | Non-NEMA |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identification and ratings are permanently fastened to the device housing

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 1686(1, 2, 3, Green)

Series
Style
Type

UL 1686 Class 1 Insulgrip®
Standard Service, Style 2

- Watertight Receptacle
- Watertight Receptacle

UPC

783585011509



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL4200RS2W-SPEC-EN | REV 1/2024