

Straight Blade Devices, Female Connector Body, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 125V, 20A5-20R

By Hubbell Wiring Device-Kellems
Catalog # [HBL15W33](#)

Straight Blade Female Connector Body, Elasto-Grip Watertight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 125V, 20A5-20R

Application

- Industrial/Commercial

Performance

- Electrical:Current Interrupting: Certified for current interrupting at full rated current
- Dielectric Voltage: Withstands 2,000V minimum
- Mechanical:Terminal Accommodation #18-#12 AWG. Stranded copper wire only.Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental:Flammability :UL 94 HB or better
- IP Suitability :IP55
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	HBL15W33
Color	Yellow
Cord Range	0.300"-0.655" (7.6-16.6)
EU RoHS Indicator	No
Environmental Conditions	Watertight
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Elastogrip
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none"> Assembly Screws - Plated steel Contact Holder - Nylon Contacts - .040" (1.0) Brass Housing - Thermoplastic Elastomer Terminal Clamp - Nickel plated steel Terminal Retainer - Clear Polycarbonate



Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585013343

Dimensions

Dimensions	3.00 in x 1.61 in x 3.00 in
Display Size	Standard
Height	3 in
Length	3 in
Weight	0.3 lb
Width	1.61 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> CSA Certified to C22.2 No. 42 File 280C NEMA® WD-6 Compliant UL Listed to UL498 File E1706
Nema Rating	5-20R

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10
Pallet Quantity 1100

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL15W33](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL15W33-SPEC-EN | REV 10/2024