

# Straight Blade Devices, Thermoplastic Elastomer Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R.



By Hubbell Wiring Device-Kellems  
Catalog # [HBL15W33A](#)

Straight Blade Thermoplastic Elastomer Watertight,  
Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding,  
20A 125V, 5-20R

## Performance

- Electrical :Current Interrupting: Rated for current interruption per UL498
- Dielectric Voltage: 2500V AC
- Max Working Voltage: As marked
- Temperature Rise: 30°C max per UL498 at rated current
- Mechanical: Cord Accomodation 0.375"-0.625" (9.5-15.9)
- Environmental: Moisture Resistance: UL Listed 4, 4X, 12, 6, 6P
- Operating temperatures: -40°C (without impact) to +60°C continuous
- UV resistance: All exposed materials are UV stabilized

## General

Catalog Number	HBL15W33A
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Operating Temperature	-40°C (without impact) to +60°C continuous
Series	Watertight Devices
Temperature Rating	-40°C (without impact) to +60°C continuous
Type	Connector Body
UPC	783585131269

## Dimensions

Weight	0.2 lb
--------	--------

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP69K rating</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA WD-1, WD-6 And ANSI Standards</li><li>• UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P</li></ul>
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	25
Pallet Quantity	1375

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Watertight Wiring Devices Flyer](#)
- [Specifications - HBL15W33A](#)
- [Warranty - Industrial & Commercial Products](#)