

## Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 20A 3-Phase Delta 600V AC, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL420C5W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 20A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, Terminal Screws, Black, Watertight

### Application

- High Ampacity Connections

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

### General

Catalog Number	HBL420C5W
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Cord Clamps - Reinforced Thermoplastic Polyester</li> <li>• Covers - Reinforced Thermoplastic Polyester</li> <li>• Gaskets - Solid Neoprene</li> <li>• Glands - Solid Neoprene</li> </ul>

Style	Housing - Zytel® ST801 Nylon
Temperature Rating	Standard Service Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585404301

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC

### Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified File LR280C</li> <li>• UL Classified to IEC 60309-1 IEC 60309-2</li> <li>• UL Listed, File E146033</li> </ul>
Nema Rating	Non-NEMA

### Logistics

Carton Quantity	10
Pallet Quantity	320

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL420C5W-SPEC-EN | REV 10/2024