

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Safety Shroud, Angled Receptacle,  
20 250V, 2-Pole 3-Wire Grounding,  
L6-20R, Screw Terminal, Gray**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2320AR](#)

Locking Devices, Twist-Lock®, Safety-Shroud®, Angled  
Receptacle, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-  
20R, Screw Terminal, Gray.



## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL2320AR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Body Contact Carrier - Natural (white) nylon</li><li>• Body Holding Screws - Steel, zinc plated</li><li>• Contacts - Brass</li><li>• Housing / Flange - Gray RPT</li><li>• Mounting Plate - Steel, zinc plated</li><li>• Terminal Retainer - Clear polycarbonate</li></ul>
Type	Angled Receptacle
UPC	783585234083

## Dimensions

Dimensions	4.77 in x 2.85 in x 3.14 in
Display Size	Standard Sized Product
Height	3.14 in
Length	4.77 in
Weight	0.7 lb
Width	2.85 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL2320AR](#)  
[Warranty - Industrial & Commercial Products](#)

