

Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL4585C](#)



Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, NEMA L6-15R, Screw Terminal, Nylon casing, Back wired, White.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL4585C
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Grounding Insulgrip® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - zinc plated • Contacts - Brass • Housing - Nylon • Mounting Screw - Nickel plated brass • Terminal Clamp - #8-32 Brass (Phillips / Slotted / Robertson) • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate
Type	Flanged Receptacle

UPC

783585170152

Dimensions

Dimensions	2.56 in x 2.56 in x 1.72 in
Display Size	Standard Sized Product
Height	1.72 in
Length	2.56 in
Weight	0.1 lb
Width	2.56 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec.W-C-596 • Listed to UL 498
Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	4050

Product Assets



A Hubbell brand