

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Industrial, Receptacle, 20A 250V, 2-
Pole 3-Wire Grounding, L6-20R,
Screw Terminal, Gray**

By Hubbell Wiring Device-Kellems
Catalog # [HBL2320SW](#)

Locking Devices, Twist-Lock®, Industrial, Watertight Safety-
Shroud® Receptacle, 20A 250V, 2-Pole 3-Wire Grounding,
NEMA L6-20R, Screw Terminal, PBT housing and flange, Gray.



Application

Heavy Duty Industrial Shrouded Watertight

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2320SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	2
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Body Contact Carrier - Natural (white) nylon• Contacts - Brass• Drive Screws - Steel, zinc plated• Housing / Cover - Gray RPT• Lift-Cover Spring & Pin - Stainless Steel• Terminal Retainer - Clear polycarbonate
Type	Receptacle

UPC

783585231082

Dimensions

Dimensions	3.75 in x 3.75 in x 2.69 in
Display Size	Standard Sized Product
Height	2.69 in
Length	3.75 in
Weight	0.55 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L6-20R

Logistics

Carton Quantity	5
Pallet Quantity	1000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2320SW](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2320SW-SPEC-EN | REV 10/2024