

Heavy Duty Products, Indulgrip Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 600V AC,

By Hubbell Wiring Device-Kellems
Catalog # [HBL460MIFS2W](#)

Heavy Duty Products, Indulgrip Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding, Terminal Screws

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000VAC Min.
- Electrical - Max. Working Voltage - 250VDC/600VAC
- Electrical - Operations - Mechanical 10,000 cycles minimum
- Environmental - Flammability - UL94-5VA and V-0 Classification
- Environmental - Ingress Protection - IP66 Suitability
- Environmental - Operating Temperatures - Max. Continuous +60°C
- Min. Continuous -40°C w/o impact
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustable feet
- Mechanical - Product Identification - Ratings are part of the external label and molded into the receptacle housing
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBL460MIFS2W
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Fused
Specifications	<ul style="list-style-type: none"> • Base,Door and Handle - Valox® • Enclosure Gasket - Neoprene



Style
Type
UPC

- Enclosure Screws - Stainless Steel
 - Ground Plate - Galvanized Steel
 - Hinge Pin - Nickel-Plated Brass
 - Shaft - Brass
- Style 2;Indulgrip
Mechanical Interlock
783585514901

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single/Three
Voltage Rating	600 VAC/250 VDC
Voltage Rating Description	600V AC/250V DC
Wattage	36000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed for US and Canada
Nema Rating	Non-NEMA

Logistics

Carton Quantity	1
-----------------	---

Product Assets



A Hubbell brand