

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 600V AC, Style 2 , Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL460PS2W](#)



Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 600V AC, 3-Pole 4-Wire Grounding Style 2, Terminal Screws, Gray and Black, Watertight

Application

- Metallic with Nylon Shroud

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability (Enclosure) - UL 94V-0 and CSA C22.2 No. 0.17
- Environmental - Moisture Resistance - Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94
- Environmental - Operating Temperatures - Max. Continuous 75°C
- Min. -40°C w/o impact -25° with impact
- Mechanical - Impact Resistance - Per CSA C22.2, No. 182.1, UL 1682
- Mechanical - Product Identification - Identification and ratings are permanently fastened to the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 1686(1, 2, 3, Green)

General

Catalog Number	HBL460PS2W
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	UL 1686 Class 1 Insulgrip®
Specifications	<ul style="list-style-type: none">• Clamp Nut - Nickel Plated Brass• Gland Cap - Rynite® SST35• Housing - Valox® 357• Plug Shroud - Aluminum• Retainer - Thermoset Polyester

Style	Standard Service, Style 2
Type	Watertight Plug
UPC	783585010601

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Voltage Rating	600 VAC/250 VDC
Voltage Rating Description	600V AC/250V DC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#6 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to CSA Spec. C22.2 No. 159• UL Listed and CSA Certified Type 4X• UL Standard 1682, UL 50, and UL 1010
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL460PS2W](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL460PS2W-SPEC-EN | REV 10/2024