

## Locking Devices, Twist-Lock®, Corrosion Resistant Insulgrip® Plug, 20A, 250V AC, 2 Pole, 3 Wire Grounding, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL23CM21](#)



Locking Devices, Twist-Lock®, Corrosion Resistant Insulgrip® Plug, 20A, 250V AC, 2 Pole, 3 Wire Grounding, Yellow

### Application

Extra Heavy Duty Industrial

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL23CM21
Color	Yellow
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Corrosion Resistant Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Stainless Steel</li><li>• Blades - Nickel Plated Brass</li><li>• Housing / Cord Clamp - Nylon</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li></ul>

UPC

- Terminal Retainer - Clear polycarbonate
  - Terminal Screws - #10-32 Bronze (Phillips / Slotted / Robertson)
- 783585038117

### Dimensions

Dimensions	2.75 in x 1.97 in x 1.97 in
Display Size	Standard Sized
Height	1.97 in
Length	2.75 in
Weight	0.25 lb
Width	1.97 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

### Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L6-20P
Standards - RoHS Compliance Status	CM

### Logistics

**Product Assets**



**A Hubbell brand**