

# Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Stainless Steel

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4715](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15R, Screw Terminal, Stainless Steel Casing, Brown/Stainless .

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL4715
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Stainless Steel Flanged Receptacle
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Blades - Brass</li><li>• Flange - Stainless steel</li><li>• Mounting Screw - Nickel plated brass</li><li>• Terminal Screws - Brass</li></ul>
Type	Flanged Receptacle
UPC	783585236766

## Dimensions

Dimensions	2.31 in x 1.75 in x 1.36 in
Display Size	Standard Sized Product
Height	1.36 in
Length	2.31 in
Weight	0.15 lb
Width	1.75 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed. Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL4715](#)  
[Warranty - Industrial & Commercial Products](#)