

Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 125/250V 3- Pole 4-Wire Grounding, L14-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2411S](#)



Locking Devices, Twist-Lock®, Industrial, Male Safety-Shroud® Plug, 20A 125/250V 3- Pole 4-Wire Grounding, NEMA L14-20P, Screw Terminal, Black and White Nylon body, White PBT Shroud.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2411S
Color	Black, White
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2 (1)
Item Type	20A Male Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Blades - Brass • Housing / Cord Clamp - Nylon • Safety-Shroud® - White PBT • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate • Terminal Screws - #10-32 Brass (Phillips / Slotted /

Type	Robertson)
UPC	Plugs 783585234465

Dimensions

Dimensions	2.33 in x 2.33 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.33 in
Weight	0.4 lb
Width	2.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L14-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity

10

Catalogs - WDK Catalog Full 2024

Specifications - HBL2411S

Warranty - Industrial & Commercial Products

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2411S-SPEC-EN | REV 10/2024