

Replaced by HBL4P105NM, Surge Protective Devices, Surface Mount Block, 100KA, 3-Phase 120/208V AC

By Hubbell Wiring Device-Kellems
Catalog # [HBL4W100C](#)



Surge Protective Devices, Surface Mount Block, 100KA, 3-Phase 120/208V AC

General

Application	Surface Mount Brick with Leads
Catalog Number	HBL4W100C
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	Green Status LED, Audible Alarm
Item Type	Wired-In Branch Panel Protection
Material	Steel
Material - Mounting Hardware	Mounting Screws
Operating Temperature	-40 Degrees F to 149 Degrees F (-40 C to 65 C)
Performance	Electrical - Diagnostics - Green Status LED's, Audible Alarm, Dry Contacts Electrical - Surge Current per Phase - 100kA Environmental - Operating Temperature - -40°F to 140°F (-40°C to 60°C) Mechanical - Terminal Accommodation - #10 AWG 18.0" Wire Leads
Response Time	5
Series	Wired-In Panels
Type	100kA
UPC	783585120799

Dimensions

Display Size	100kA Peak
--------------	------------

Electrical Ratings

Connectivity	Leads
Frequency Rating	60 Hz
Phase	Three Phase
Voltage Rating	Wye 120 VAC Wye 208 VAC
Voltage Rating Description	120/208 VAC Wye

Certifications And Compliance

Industry Standard(s)	cULus UL1449-3Rd Edition Type 2 Spd
----------------------	-------------------------------------

Logistics

Carton Quantity	1
Pallet Quantity	216

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Warranty - SPD Series: 320kA, 160kA, 100kA, 120kA, 80MkA & 50kA](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL4W100C-SPEC-EN | REV 6/2024