



# Locking Devices, Twist-Lock®, Safety Shroud, Surface Mount Receptacle, 20A 3-Phase Delta 250V AC, 3-Pole 4- Wire Grounding, L15-20R, Screw Terminal

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2420SR](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, Surface Mount Receptacle, One Gang, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Screw Terminal, Gray.

## Features

- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Engineered thermoplastic housing is impact and corrosion resistant, making it suitable for heavy-duty industrial environments

## Application

Heavy Duty Industrial Shrouded

## General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)</li> </ul>

## Dimensions

Dimensions	4.56 in x 2.84 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	4.56 in
Weight	0.50 lb
Width	2.84 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3-Phase Delta 250 VAC
Voltage Rating Description	3-Phase Delta 250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L15-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Wiring B-23](#) [Catalog Page Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Surface Mount Receptacle
- Surface Mount Receptacle

UPC

783585234502



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL2420SR-SPEC-EN | REV 1/2024