

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15- 20P, Screw Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2425](#)



Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15- 20P, Screw Terminal, Nylon casing, Back wired, White.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Cord Grip Accomodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2425
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Insulation	Insulated Body
Item Type	20A Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Blades - Brass • Housing - Nylon • Mounting Screw - Nickel plated brass • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate

Temperature Rating

Type
UPC

Dimensions

Dimensions	3.06 in x 3.06 in x 2.27 in
Display Size	Standard Sized Product
Height	2.27 in
Length	3.06 in
Weight	0.25 lb
Width	3.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L15-20P

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Maximum Continuous: 75° C;
Minimum Continuous: -40° C w/o impact, -25° with impact.
Flanged Inlet
783585038247

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL2425](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2425-SPEC-EN | REV 10/2024