

Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5- 15R, Blue

By Hubbell Wiring Device-Kellems
Catalog # [HBL5260SA](#)



Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle
with Light, 15A 125V, 5-15R, Blue

General

Application	Decorator Duplex
Catalog Number	HBL5260SA
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	None
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	Electrical - Protection Modes - Normal and Common Modes Electrical - Response Time - Approximately 5 ns Electrical - Transient Suppression - Peak Energy (10 X 100 Qs), Peak Current (8 X 20 Qs) Electrical - Voltage - 120V AC + 10% - 15% Environmental - Flammability - UL 94V-2 Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Specification Grade
Type	Duplex Duplex
UPC	783585060019

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	CSA Certified to Specification C22.2 No. 42 Listed to UL Standards 498 UL Listed File E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	3500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5260SA-SPEC-EN | REV 6/2024