

# Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5- 15R, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5260WSA](#)



Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle  
with Light, 15A 125V, 5-15R, White

## Application

Decorator Duplex

## Performance

- Electrical - Protection Modes - Normal and Common Modes
- Electrical - Response Time - Approximately 5 ns
- Electrical - Transient Suppression - Peak Energy (10 X 100 Qs), Peak Current (8 X 20 Qs)
- Electrical - Voltage - 120V AC + 10% - 15%
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

## General

Catalog Number	HBL5260WSA
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	None
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Specifications	<ul style="list-style-type: none"><li>• Base Material - Nylon</li><li>• Contact Design - Tandem Modified Bypass</li><li>• Face Material - Nylon</li><li>• Mounting Strap - .050" (1.3) Steel-Zinc Coated</li></ul>

- Power Contact - .031" (.8)  
Brass
- Type  
UPC  
Duplex  
783585219905

## Dimensions

Display Size Standard

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified to Specification C22.2 No. 42</li><li>• Listed to UL Standards 498</li><li>• UL Listed File E2186</li></ul>
Nema Rating	5-15R

## Logistics

Carton Quantity 10

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Residential Catalog](#)  
[Specifications - HBL5260WSA](#)  
[Warranty - Industrial & Commercial Products](#)