


## Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5262GY](#)



Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack.

### Application

- Extra Heavy Duty Specification Grade

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL5262GY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Automatic Self-grounding Clip - Stainless steel</li> <li>• Base - PBT</li> <li>• By-Pass Power Contacts - .036". (.9) Brass</li> <li>• Clamping Plate - Nickel plated brass</li> <li>• Face - Nylon</li> </ul>

- Ground Contacts - .031 in. (.8) Brass
  - Mounting Screws - Zinc plated steel
  - Mounting Strap - .050 in. (1.3) Brass
  - Terminal Screws - Plated brass
- Finder Groove Face  
Standard Duplex  
783585435145

Style  
Type  
UPC

### Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA 22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> </ul>
----------------------	--

Nema Rating 5-15R  
Standards - RoHS Compliance Status CM  
• UL Listed to UL498 File No. E2186

Carton Quantity 10  
Pallet Quantity 5500

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL5262GY](#)  
[Warranty - Industrial & Commercial Products](#)

**Logistics**

