

## Locking Devices, Twist-Lock®, Elastogrip, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing



By Hubbell Wiring Device-Kellems  
Catalog # [HBL24W47](#)

Locking Devices, Twist-Lock®, Elastogrip®, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15P, Screw Terminal, Yellow Elastomer, Water/Dust-Tight Housing.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG- #10 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL24W47
Color	Yellow
Cord Range	0.300"-.655"(7.6-16.6)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Watertight
Horsepower - Maximum	0.5
Item Type	15A Grounding Elastogrip® Plug
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel, zinc plated</li><li>• Blades - Brass</li><li>• Strain Relief Nut - Nylon</li><li>• Terminal Retainer - Clear polycarbonate</li><li>• Terminal Screws - Brass</li></ul>
Type	Plugs
UPC	783585235844

### Dimensions

Dimensions	1.55 in x 1.55 in x 2.65 in
Display Size	Standard Sized
Height	2.65 in
Length	1.55 in
Weight	0.2 lb
Width	1.55 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

### Conductor Related

Cable Range	0.300 - 0.655 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L5-15P
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	4050



A Hubbell brand