

Locking Devices, Twist-Lock®, Elastogrip® Connector, 15A, 125V, 2 Pole, 3 Wire Grounding, NEMA L5-15R, yellow elastomer, dust tight

By Hubbell Wiring Device-Kellems
Catalog # [HBL2547](#)

Locking Devices, Twist-Lock®, Elastogrip® Connector, 15A, 125V, 2 Pole, 3 Wire Grounding, NEMA L5-15R, yellow elastomer, dust tight

Application

Heavy Duty Industrial

Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 2,000V minimum
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

General

Catalog Number	HBL2547
Color	Yellow
Cord Range	0.300"-0.655"(7.6-16.6)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Elastogrip® Connector
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel, zinc plated• Contacts - Brass• Cord Clamp - Nylon



Temperature Rating

UPC

Dimensions

Dimensions	4.00 in x 1.76 in x 4.00 in
Display Size	Standard
Height	4 in
Length	4 in
Weight	0.2 lb
Width	1.76 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L5-15R

Logistics

- Cord Clamp Screws - Steel, zinc plated
 - Terminal Retainer - Clear polycarbonate
 - Terminal Screws - Brass
- Maximum Continuous: 75° C;
Minimum Continuous: -40° C w/o impact, -25° with impact.
783585235905

Product Assets



A Hubbell brand