


# Straight Blade Devices, Receptacles, Weather-Resistant Duplex, Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5262GYWR](#)



Straight Blade Receptacle, Weather-Resistant Duplex, Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

## Application

- Extra Heavy Duty Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL5262GYWR
Color	Gray
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Clip - Stainless steel</li><li>• Base - PBT</li><li>• By-Pass Power Contacts - .036". (.9) Brass</li><li>• Clamp - Brass</li><li>• Contacts - 0.031" (0.8) Brass</li><li>• Face - Nylon</li></ul>

Style  
Type  
UPC

- Mounting Screws - Stainless Steel
  - Terminal Screws - Brass
- Finder Groove Face  
Weather Resistant  
783585320519

## Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42 File 285</li><li>• Fed. Spec. WC596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-15R

Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 10

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - EdgeConnect™ Technology FAQ](#)

[Specifications - HBL5262GYWR](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL5262GYWR-SPEC-EN | REV 10/2024