

Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 30A 250V, 2-Pole 3-Wire Grounding, L6-30P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL2621S](#)

Locking Devices, Twist-Lock®, Safety-Shroud®, Male Plug, 30A 250V AC, 2-Pole 3-Wire Grounding, L6-30P, Screw Terminal, Black and White Nylon Body, White PBT Shroud.

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2621S
Color	Black, White
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated• Blades - Brass• Housing / Cord Clamp - Nylon• Safety-Shroud® - White PBT

Type
UPC

- Terminal Clamp - Cold rolled steel - nickel plated
 - Terminal Retainer - Clear polycarbonate
 - Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Plugs
783585234380

Dimensions

Dimensions	2.26 in x 2.26 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.26 in
Weight	0.9 lb
Width	2.26 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42
----------------------	--

Nema Rating
Standards - RoHS Compliance
Status

- Fed.Spec. W-C-596
- Listed to UL 498

L6-30P
CM

Carton Quantity 10
Pallet Quantity 2240

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2621S](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand