

Straight Blade Devices, Receptacles, Single, Marine Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack, Chem- Marine

By Hubbell Wiring Device-Kellems
Catalog # [HBL52CM61](#)

Straight Blade Devices, Receptacles, Single, Marine Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack, Chem-Marine.



Application

Extra Heavy Duty Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL52CM61
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Corrosion resistant
Horsepower - Maximum	0.5
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	HBL Extra Heavy Duty
Specifications	<ul style="list-style-type: none"> • Auto Self-grounding Clip - Stainless steel • Base - PBT • Face - Nylon • Ground Contact - Brass • Mounting Screws - Stainless steel

Style

Type
UPC

Dimensions

Dimensions	3.28 in x 1.63 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596
----------------------	--

- Mounting Strap - .050" (1.3) Nickel plated brass
 - Power Contacts - .037 in. (.9) Nickel plated brass
 - Weather and Corrosion Resistant
 - Finder Groove Face
- Single Receptacle
783585808260

- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Carton Quantity 10
Pallet Quantity 840

Nema Rating 5-15R
Standards - RoHS Compliance CM
Status

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL52CM61](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL52CM61-SPEC-EN | REV 10/2024