

Straight Blade Devices, Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 125V, 15A 5-15P, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL52CM66C](#)

Straight Blade Devices, Male Plug, Corrosion Resistant,
Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding,
125V, 15A 5-15P, Yellow, Single Pack.

Application


- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL52CM66C
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless steel• Blade Holder - Nylon• Blades - .060 in. (1.5) Nickel plated brass• Housing - Nylon• Terminal Clamp - Nickel plated steel• Terminal Retainer - Clear Polycarbonate



Style
Type
UPC

- Terminal Screws - #8-32 Brass , multiple drive
- Corrosion Resistant
Plugs
783585161501

Dimensions

Dimensions	1.52 in x 1.52 in x 1.96 in
Height	1.96 in
Length	1.52 in
Weight	0.2 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to C22.2 No. 42 File 280• NEMA® WD-6 Compliant• UL Listed to UL498 File E1706
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 10
Pallet Quantity 840

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL52CM66C](#)
[Warranty - Industrial & Commercial Products](#)

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL52CM66C-SPEC-EN | REV 10/2024