

Locking Devices, Twist-Lock®, Safety-Shroud® Plug, 30A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding, NEMA L21-30P and white nylon body PBT shroud



By Hubbell Wiring Device-Kellems
Catalog # [HBL2811S](#)

Twist-Lock®, Safety-Shroud® Plug, 30A, 3 Phase Y 120/208V AC, 4-Pole, 5 Wire Grounding, NEMA L21 and white nylon body, white PBT shroud

Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

General

Catalog Number	HBL2811S
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	30A Safety-Shroud® Plug
Listings	<ul style="list-style-type: none"> • UL 498 • Fed.Spec. W-C-596 • CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Blades - Brass • Housing / Cord Clamp - Nylon • Safety-Shroud® - White PBT

UPC

- Terminal Clamp - Cold rolled steel - nickel plated
 - Terminal Retainer - Clear polycarbonate
 - Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- 783585235103

Dimensions

Dimensions	2.33 in x 2.33 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.33 in
Weight	0.45 lb
Width	2.33 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	120/208 VAC
Voltage Rating Description	120/208 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	5-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating L21-30P

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL2811S](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2811S-SPEC-EN | REV 10/2024