



# IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL332C6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight



## Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

## Application

High Ampacity Connections

## General

Color	Blue
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"><li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li><li>• Electrical - Dielectric Voltage - 3000V AC</li><li>• Electrical - Max. Working Voltage - 600V RMS</li><li>• Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17</li><li>• Environmental - Ingress Protection - IP67 Suitability</li><li>• Environmental - Moisture Resistance - Watertight per IEC 60309-1</li><li>• Environmental - Operating Temperatures - Maximum Continuous 75°C</li><li>• Minimum - 40°C w/o impact</li><li>• Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682</li><li>• Mechanical - Product</li></ul>

## Dimensions

Display Size	Standard
--------------	----------

## Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Voltage Rating	220-240 VAC
Voltage Rating Description	220-240 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified File LR280C</li><li>• UL Classified to IEC 60309-1 IEC 60309-2</li><li>• UL Listed, File E146033</li></ul>
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

	Identification - Identification and ratings are a permanent part of the device housing
	<ul style="list-style-type: none"><li>Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions</li></ul>
Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585403670



A proud member of the Hubbell Family.