

Straight Blade Devices, Receptacles, Tamper Resistant, Duplex, Industrial Grade, 2-Pole 3- Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362GYTR](#)



Straight Blade Devices, Receptacles, Tamper Resistant, Duplex,
Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R,
Gray, Single Pack

Application

Extra Heavy Duty Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5362GYTR
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Item Type	Traditional Duplex
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - .04 in. (.91) C688 Brass• Mounting Screws - Galvanized Steel• Mounting Strap - .047 in. Brass

- Power Contacts - .032 in. (.81) C688 Brass
 - Terminal Screws - Plated steel
 - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Smooth Face
Tamper-Resistant
783585542508

Style
Type
UPC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Weight	0.2 lb
Width	1.32 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified 22.2, No. 42• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-20R

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5362GYTR](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5362GYTR-SPEC-EN | REV 1/2025