

Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362I](#)



Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack

Application

- Extra Heavy Duty Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5362I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - PBT• By-Pass Power Contacts - .036". (.9) Brass• Clamping Plate - Nickel plated brass• Face - Nylon

Style
Type
UPC

- Ground Contacts - .031 in. (.8) Brass
 - Mounting Screws - Zinc plated steel
 - Mounting Strap - .050 in. (1.3) Brass
 - Terminal Screws - Plated brass
- Finder Groove Face
Standard Duplex
783585435282

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA 22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant
----------------------	--

Nema Rating
Standards - RoHS Compliance
Status

- UL Listed to UL498 File No. E2186

5-20R
CM

Carton Quantity 10
Pallet Quantity 3600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5362I](#)
[Warranty - Industrial & Commercial Products](#)

Logistics

