



# Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3- Phase Wye 120/208V AC, 4-Pole 4-Wire Non- Grounding, Non-NEMA, Screw Terminal

By Hubbell Wiring Device-Kellems  
Catalog # [HBL3430](#)



Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3- Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black.

## Features

- High-impact, abuse-resistant nylon face
- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

## Application

Heavy Duty Industrial

## General

|                              |  |
|------------------------------|--|
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means  |
| Item Type                    | 30A Non-Grounding Single Flush Receptacle  |
| Material                     | Nylon  |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 4-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact   |
| Performance                  | <ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal</li> </ul> |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 3.61 in x 1.71 in x 1.36 in |
| Display Size | Standard Sized Product      |
| Height       | 1.36 in                     |
| Length       | 3.61 in                     |
| Weight       | 0.25 lb                     |
| Width        | 1.71 in                     |

## Electrical Ratings

|                            |                            |
|----------------------------|----------------------------|
| Amperage Rating            | 30 A                       |
| Connectivity               | Back Wired Screw Terminals |
| Current / Amperage Rating  | 30 A                       |
| Current Rating             | 30 A                       |
| Dielectric Strength        | Withstands 2,000V minimum  |
| Phase                      | Three Phase                |
| Voltage Rating             | 3 Phase WYE 120/208 VAC    |
| Voltage Rating Description | 3 Phase WYE 120/208 VAC    |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #16 AWG to #8 AWG |

## Certifications and Compliance

|                                    |   |
|------------------------------------|---|
| Industry Standard(s)               | <ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul> |
| Nema Rating                        | Non-NEMA  |
| Standards - RoHS Compliance Status | CM  |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Accommodation - #16  
AWG - #8 AWG solid or  
stranded copper wire only.

- Mechanical - Terminal  
Identification - Terminals  
identified in accordance  
with UL 498

Type

- Single Flush Receptacle
- Single Flush Receptacle

UPC

783585333205



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL3430-SPEC-EN | REV 1/2024