

Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362ISA](#)



Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Ivory

Application

- Decorator Duplex with Light and Alarm

Performance

- Electrical - Protection Modes - Normal and Common Modes
- Electrical - Response Time - Approximately 5 ns
- Electrical - Transient Suppression - Peak Energy (10 X 100 Qs), Peak Current (8 X 20 Qs)
- Electrical - Voltage - 120V AC + 10% - 15%
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

General

Catalog Number	HBL5362ISA
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Specifications	<ul style="list-style-type: none"> • Base Material - Nylon • Contact Design - Tandem Modified Bypass • Face Material - Nylon • Mounting Strap - .050" (1.3) Steel-Zinc Coated

Type	Duplex
UPC	783585060279
	• Power Contact - .031" (.8) Brass

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 • UL Listed File E2186
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5362ISA](#)
[Warranty - Industrial & Commercial Products](#)