




Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Flanged Inlet, 60A 250V AC, 2-Pole 3- Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL360B6W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Flanged Inlet, 60A 250V AC, 2-Pole 3- Wire Grounding, Terminal Screws, Blue, Watertight

Application

High Ampacity Watertight Connections

General

Color	Blue
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none">• Electrical - Current Interrupting - Certified for current interrupting at full rated current• Electrical - Dielectric Voltage - Withstand 3000V AC• Electrical - Max. Working Voltage - 600V RMS• Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17• Environmental - Ingress Protection - IP67 Suitability• Environmental - Moisture Resistance - Watertight per IEC 60309-1• Environmental - Operating Temperatures - Maximum Continuous 75°C• Minimum - 40°C w/o impact• Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682• Mechanical - Product Identification - Ratings are a permanent part of the device housing• Mechanical - Terminal

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 3000V Minimum in
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC
Wattage	15000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#8 AWG to #2 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed, File E146032
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identification - Terminals
identified in accordance
with North American and
IEC conventions

Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Watertight Inlet
UPC	783585403748



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL360B6W-SPEC-EN | REV 1/2024